

Flat suction cup (round)

PFG 3.5 NBR-55 N003


Art.-Nr.: 10.01.01.00004



PFG 3.5 NBR-55 N003

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	3.50



Design data

Attribute	Value
Height H2	1.50 mm
Height H	4.00 mm
Head diameter Dk	4.2 mm
Internal diameter d1	3.0 mm
Internal diameter d	2.00 mm
Spring stroke Z	0.5 mm
Diameter Ds	3.5 mm
Height H3	2.50 mm
Diameter Dmax(S)	4.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFG 3.5 NBR-55 N003



WWW.SCHMALZ.COM/10.01.01.00004

Flat suction cup (round)

PFG 3.5 NBR-55 N003



Art.-Nr.: 10.01.01.00004



Technical data

Attribute	Value
Nipple family	N 003
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	7.5 mm
Suction force (-600mbar)	0.42 N
Volume	0.015 cm ³
Size	3.50
Product family	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00004



Ordering Data Accessories 10.01.01.00004

Typ	Item number
Suction cup connection nipple	SA-NIP N003 M3-AG DN100 10.01.01.00316



WWW.SCHMALZ.COM/10.01.01.00004