

Düz vantuz (yuvarlak)

PFG 8 PU-55 N004


Art.-Nr.: 10.01.01.00049



PFG 8 PU-55 N004

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	8,00



Tasarım verileri PFG 8 PU-55 N004

Tasarım verileri

Attribute	Value
Yükseklik H2	2,00 mm
Yükseklik H	7,00 mm
Kafa çapı Dk	8,2 mm
İç çap d1	6,0 mm
İç çap d	4,00 mm
Yay stroku Z	1,3 mm
Çap Ds	8,0 mm
Yükseklik H3	4,00 mm
Çap Dmax(S)	9,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00049

Art.-Nr.: 10.01.01.00049

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 004
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	10,0 mm
Emme kuvveti (-600mbar)	2,30 N
Ağırlık	0,20 g
Cilt	0,155 cm ³
Boyut	8,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00049

**Sipariş Verisi Aksesuarlar 10.01.01.00049**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N004 G1/8-AG DN200
Vantuz bağlantı nipel	SA-NIP N004 G1/8-IG DN200
Vantuz bağlantı nipel	SA-NIP N004 M5-AG DN200
Vantuz bağlantı nipel	SA-NIP N004 M5-IG DN200

