

Düz vantuz (yuvarlak)

PFG 60 PU-55 N009 M10x1.25-IG




Art.-Nr.: 10.01.01.00058



PFG 60 PU-55 N009 M10x1.25-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	60,00



Tasarım verileri

Attribute	Value
Yükseklik H	18,00 mm
Kafa çapı Dk	38,7 mm
Yay stroku Z	4,7 mm
Çap Ds	60,0 mm
Çap Dmax(S)	64,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri PFG 60 PU-55 N009 M10x1.25-IG



WWW.SCHMALZ.COM/10.01.01.00058

Düz vantuz (yuvarlak)

PFG 60 PU-55 N009 M10x1.25-IG



Art.-Nr.: 10.01.01.00058



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 009
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	100,0 mm
Emme kuvveti (-600mbar)	125,00 N
Ağırlık	24,10 g
Cilt	11,846 cm ³
Boyut	60,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00058



Sipariş Verisi Aksesuarlar 10.01.01.00058

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N009 G1/4-AG
Vantuz bağlantı nipel (inst)	SA-NIP N009 G1/4-IG
Vantuz kapağı	SU 60



WWW.SCHMALZ.COM/10.01.01.00058