

Düz vantuz (yuvarlak)

PFG 20 FPM-65 N006




Art.-Nr.: 10.01.01.00072



PFG 20 FPM-65 N006

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	20.00
Malzeme özelliği	iz bırakmayan



Tasarım verileri PFG 20 FPM-65 N006

Tasarım verileri

Attribute	Value
Yükseklik H2	4.50 mm
Yükseklik H	10.00 mm
Kafa çapı Dk	15.2 mm
İç çap d1	11.0 mm
İç çap d	4.50 mm
Yay stroku Z	2.2 mm
Çap Ds	20.0 mm
Çap Dmax(S)	23.0 mm
Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları	



WWW.SCHMALZ.COM/10.01.01.00072

Art.-Nr.: 10.01.01.00072

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 006
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65.0 Shore A
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Emme kuvveti (-600mbar)	15.50 N
Ağırlık	2.5 g
Cilt	0.864 cm ³
Boyut	20.00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00072

**Sipariş Verisi Aksesuarlar 10.01.01.00072**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N006 G1/8-AG DN200
Vantuz bağlantı nipeli	SA-NIP N006 G1/8-IG DN200

