

Flat suction cup (round)

PFG 35 FPM-65 N007


Art.-Nr.: 10.01.01.00075



PFG 35 FPM-65 N007

Technical data

Attribute	Value
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Size	35.00
Material property	non-marking



Design data PFG 35 FPM-65 N007

Design data

Attribute	Value
Height H2	7.00 mm
Height H	14.00 mm
Head diameter Dk	20.5 mm
Internal diameter d1	11.0 mm
Internal diameter d	6.00 mm
Spring stroke Z	3.0 mm
Diameter Ds	35.0 mm
Diameter Dmax(S)	38.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.00075

Flat suction cup (round)

PFG 35 FPM-65 N007



Art.-Nr.: 10.01.01.00075



Technical data

Attribute	Value
Nipple family	N 007
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	44.00 N
Weight	5.8 g
Volume	2.805 cm ³
Size	35.00
Product family	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00075



Ordering Data Accessories 10.01.01.00075

Typ		Item number
Suction cup connection nipple	SA-NIP N007 G1/8-AG DN240	10.01.01.03531
Suction cup connection nipple	SA-NIP N007 G1/8-IG DN350	10.01.01.03523
Suction cup cover	SU 30	10.01.01.12889



WWW.SCHMALZ.COM/10.01.01.00075