

Düz vantuz (yuvarlak)

PFG 80 FPM-65 N009 M10x1.25-IG




Art.-Nr.: 10.01.01.00079



PFG 80 FPM-65 N009 M10x1.25-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	80,00
Malzeme özelliği	iz bırakmayan



Tasarım verileri

Attribute	Value
Yükseklik H	20,50 mm
Kafa çapı Dk	52,3 mm
Yay stroku Z	6,0 mm
Çap Ds	80,0 mm
Çap Dmax(S)	86,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri PFG 80 FPM-65 N009 M10x1.25-IG



WWW.SCHMALZ.COM/10.01.01.00079

Art.-Nr.: 10.01.01.00079

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 009
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65,0 Shore A
İş parçası yarıçapı dak (dışbükey)	150,0 mm
Emme kuvveti (-600mbar)	260,00 N
Ağırlık	69,50 g
Cilt	26,756 cm ³
Boyut	80,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00079

**Sipariş Verisi Aksesuarlar 10.01.01.00079**

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N009 G1/4-AG
Vantuz bağlantı nipel (inst)	SA-NIP N009 G1/4-IG
Vantuz kapağı	SU 80

