

Art.-Nr.: 10.01.01.00135




PFYN 80 FPM-65 G1/4-IG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP



Design data PFYN 80 FPM-65 G1/4-IG

Technical data

Attribute	Value
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Size	80.00
Vacuum connection	G1/4"-F

Design data

Attribute	Value
Height H	41.00 mm
Nominal diameter dn	5.50 mm
Thread G1	G1/4"-F
Thread length LG1	11.0 mm
Key width SW1	17.0 mm
Spring stroke Z	6.0 mm
Diameter Ds	80.0 mm
Diameter Dmax(S)	86.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.00135

**Technical data**

Attribute	Value
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Suction force (-600mbar)	260.00 N
Weight	75.00 g
Size	80.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00135

**Ordering Data Accessories 10.01.01.00135**

Typ	Item number
Suction cup cover SU 80	10.01.01.12839

**Ordering Data Spare Parts 10.01.01.00135**

Typ	Item number
Suction cup connection nipple (inst) SA-NIP N009 G1/4-IG	10.01.01.10096

**Ordering Data Wear Parts 10.01.01.00135**

Typ	Item number
Flat suction cup (round) PFG 80 FPM-65 N009 M10x1.25-IG	10.01.01.00079

