

Düz vantuz (oval)

SGO 12x4 SI-HD-65 N020




Art.-Nr.: 10.01.01.00222



SGO 12x4 SI-HD-65 N020

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
Boyutlar (LxW)	12x4



Tasarım verileri SGO 12x4 SI-HD-65 N020

Tasarım verileri

Attribute	Value
Yükseklik H2	9,30 mm
Yükseklik H	15,00 mm
Kafa çapı Dk	8,0 mm
Nominal çap dn	1,50 mm
İç çap d	4,20 mm
Yay stroku Z	0,5 mm
Vantuz genişliği Bs	4,00 mm
Ls	12,00 mm
Lmaks.(S)	13,00 mm
Bmax(S)	5,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00222

Düz vantuz (oval)

SGO 12x4 SI-HD-65 N020



Art.-Nr.: 10.01.01.00222



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
Emme kuvveti (-600mbar)	1,80 N
Ağırlık	0,50 g
Ürün ailesi	SGO
Boyutlar (LxW)	12x4

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00222



Sipariş Verisi Aksesuarlar 10.01.01.00222

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N020 M5-AG DN180
	10.01.01.00312



WWW.SCHMALZ.COM/10.01.01.00222