

Flat suction cup (round)

PFG 120 NBR-55 N010


Art.-Nr.: 10.01.01.00331



PFG 120 NBR-55 N010

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	120.00



Design data PFG 120 NBR-55 N010

Design data

Attribute	Value
Height H	23.50 mm
Head diameter Dk	89.5 mm
Internal diameter d	7.00 mm
Spring stroke Z	6.0 mm
Diameter Ds	120.0 mm
Diameter Dmax(S)	124.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.00331

Flat suction cup (round)

PFG 120 NBR-55 N010



Art.-Nr.: 10.01.01.00331



Technical data

Attribute	Value
Nipple family	N 010
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	300.0 mm
Suction force (-600mbar)	540.00 N
Weight	233.5 g
Volume	75.164 cm ³
Size	120.00
Product family	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00331



Ordering Data Accessories 10.01.01.00331

Typ	Item number
Flat suction cup (round) PFG 120 FPM-65 N010	10.01.01.00389



WWW.SCHMALZ.COM/10.01.01.00331