


Düz vantuz (yuvarlak)

PFG 120 SI-55 N010




Art.-Nr.: 10.01.01.00332



PFG 120 SI-55 N010

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	120,00
Malzeme özellikleri	FDA uyumlu



Tasarım verileri PFG 120 SI-55 N010

Tasarım verileri

Attribute	Value
Yükseklik H	23,50 mm
Kafa çapı Dk	89,5 mm
İç çap d	7,30 mm
Yay stroku Z	6,0 mm
Çap Ds	120,0 mm
Çap Dmax(S)	124,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00332

Art.-Nr.: 10.01.01.00332

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 010
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	300,0 mm
Emme kuvveti (-600mbar)	540,00 N
Ağırlık	220,30 g
Cilt	75,164 cm ³
Boyut	120,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00332

**Sipariş Verisi Aksesuarlar 10.01.01.00332**

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG
Vantuz kapağı	SU 120

WWW.SCHMALZ.COM/10.01.01.00332