


Düz vantuz (yuvarlak)

PFG 150 SI-55 N010




Art.-Nr.: 10.01.01.00334



PFG 150 SI-55 N010

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	150,00
Malzeme özellikleri	FDA uyumlu



Tasarım verileri PFG 150 SI-55 N010

Tasarım verileri

Attribute	Value
Yükseklik H	31,00 mm
Kafa çapı Dk	104,5 mm
İç çap d	7,00 mm
Yay stroku Z	9,0 mm
Çap Ds	147,5 mm
Çap Dmax(S)	158,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00334

Art.-Nr.: 10.01.01.00334

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 010
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	300,0 mm
Emme kuvveti (-600mbar)	842,00 N
Ağırlık	385,00 g
Cilt	164,707 cm ³
Boyut	150,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00334

**Sipariş Verisi Aksesuarlar 10.01.01.00334**

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG 10.01.01.00796
Vantuz kapağı	SU 160 10.01.01.12438

