


Düz vantuz (yuvarlak)

PFG 200 NBR-55 N010


Art.-Nr.: 10.01.01.00335



PFG 200 NBR-55 N010

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	200,00



Tasarım verileri PFG 200 NBR-55 N010

Tasarım verileri

Attribute	Value
Yükseklik H	37,00 mm
Kafa çapı Dk	142,5 mm
İç çap d	7,00 mm
Dmk	40,0 mm
Yay stroku Z	13,0 mm
Çap Ds	193,0 mm
Çap Dmax(S)	222,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00335

Art.-Nr.: 10.01.01.00335

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 010
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	400,0 mm
Emme kuvveti (-600mbar)	1.498,00 N
Ağırlık	671,00 g
Cilt	401,915 cm ³
Boyut	200,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00335

**Sipariş Verisi Aksesuarlar 10.01.01.00335**

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG 10.01.01.00796
Vantuz kapağı	SU 210 10.01.01.12439

