

Düz vantuz (yuvarlak)

PFG 50 VU1-72 N011


Art.-Nr.: 10.01.01.00424



PFG 50 VU1-72 N011

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72,0 Shore A
Boyut	50,00



Tasarım verileri PFG 50 VU1-72 N011

Tasarım verileri

Attribute	Value
Yükseklik H2	8,00 mm
Yükseklik H	17,00 mm
Kafa çapı Dk	18,0 mm
İç çap d1	13,0 mm
İç çap d	8,00 mm
Yay stroku Z	4,5 mm
Çap Ds	49,0 mm
Yükseklik H3	11,00 mm
Çap Dmax(S)	53,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00424

Art.-Nr.: 10.01.01.00424

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72,0 Shore A
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	95,00 N
Ağırlık	7,00 g
Cilt	6,912 cm ³
Boyut	50,00
Körük Sayısı	0,0
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00424

**Sipariş Verisi Aksesuarlar 10.01.01.00424**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N011 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N011 G1/4-IG DN350

WWW.SCHMALZ.COM/10.01.01.00424