

Düz vantuz (yuvarlak)

PFG 95 VU1-72 N012


Art.-Nr.: 10.01.01.00430



PFG 95 VU1-72 N012

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72,0 Shore A
Boyut	95,00



Tasarım verileri PFG 95 VU1-72 N012

Tasarım verileri

Attribute	Value
Yükseklik H2	12,00 mm
Yükseklik H	25,00 mm
Kafa çapı Dk	31,0 mm
İç çap d1	25,0 mm
İç çap d	12,00 mm
Yay stroku Z	6,0 mm
Çap Ds	95,0 mm
Yükseklik H3	16,50 mm
Çap Dmax(S)	101,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00430

Art.-Nr.: 10.01.01.00430

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72,0 Shore A
İş parçası yarıçapı dak (dışbükey)	140,0 mm
Emme kuvveti (-600mbar)	350,00 N
Ağırlık	58,00 g
Cilt	43,702 cm ³
Boyut	95,00
Körük Sayısı	0,0
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00430

**Sipariş Verisi Aksesuarlar 10.01.01.00430**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N012 G1/4-AG DN500
Vantuz bağlantı nipel	SA-NIP N012 G1/4-IG DN600

WWW.SCHMALZ.COM/10.01.01.00430