

Düz vantuz (oval)

SGO 4x2 NBR-55 N003



Art.-Nr.: 10.01.01.00456



SGO 4x2 NBR-55 N003

Teknik veriler


Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyutlar (LxW)	4x2

Tasarım verileri

Attribute	Value
Yükseklik H2	1,50 mm
Yükseklik H	6,00 mm
Kafa çapı Dk	6,0 mm
Nominal çap dn	1,20 mm
İç çap d	1,50 mm
Yay stroku Z	0,5 mm
Vantuz genişliği Bs	2,00 mm
Ls	4,00 mm
Lmaks.(S)	4,50 mm
Bmax(S)	2,50 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 4x2 NBR-55 N003



WWW.SCHMALZ.COM/10.01.01.00456

Düz vantuz (oval)

SGO 4x2 NBR-55 N003



Art.-Nr.: 10.01.01.00456



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Emme kuvveti (-600mbar)	0,40 N
Ağırlık	0,10 g
Ürün ailesi	SGO
Boyutlar (LxW)	4x2

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00456



Sipariş Verisi Aksesuarlar 10.01.01.00456

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N003 M3-AG DN100
	10.01.01.00316



WWW.SCHMALZ.COM/10.01.01.00456