

Flat suction cup (oval)

SGO 7x3.5 NBR-55 N003

Art.-Nr.: 10.01.01.00488



SGO 7x3.5 NBR-55 N003


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Dimension (LxW)	7 x 3.5

Design data

Attribute	Value
Height H2	1.50 mm
Height H	6.00 mm
Head diameter Dk	6.0 mm
Nominal diameter dn	1.50 mm
Internal diameter d	1.50 mm
Spring stroke Z	0.8 mm
Suction cup width Bs	3.50 mm
Ls	7.00 mm
Lmax.(S)	8.00 mm
Bmax(S)	4.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Design data SGO 7x3.5 NBR-55 N003



WWW.SCHMALZ.COM/10.01.01.00488

Flat suction cup (oval)

SGO 7x3.5 NBR-55 N003



Art.-Nr.: 10.01.01.00488



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Suction force (-600mbar)	1.00 N
Weight	0.1 g
Dimension (LxW)	7 x 3.5
Product family	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00488



Ordering Data Accessories 10.01.01.00488

Typ		Item number
Suction cup connection nipple	SA-NIP N003 M3-AG DN100	10.01.01.00316



WWW.SCHMALZ.COM/10.01.01.00488