




SPL-HT 90 FPM-F-65

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocautchuc FPM-F
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	90,00



Tasarım verileri SPL-HT 90 FPM-F-65

Tasarım verileri

Attribute	Value
Yükseklik H2	4,00 mm
Yükseklik H	36,00 mm
Kafa çapı Dk	86,0 mm
İç çap d1	78,0 mm
d2	4,0 mm
İç çap d	72,00 mm
Yay stroku Z	16,5 mm
Çap Ds	90,0 mm
Yükseklik H3	9,50 mm
Çap Dmax(S)	98,0 mm

Art.-Nr.: 10.01.01.00553



Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocautchuc FPM-F
İş parçası yarıçapı dak (dışbükey)	250,0 mm
Emme kuvveti (-600mbar)	230,00 N
Ağırlık	79,20 g
Cilt	119,000 cm ³
Boyut	90,00
Çalışma sıcaklığı maks.	350,0 °C
Ürün ailesi	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00553

