





PFYN 15 VU1-72 G1/8-IG

Suction cup PFYN VU1 (elastomer part + connection nipple) is delivered assembled. The assembly consists of:

- Suction cup of type PFG VU 1 – elastomer part, available in various diameters
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG VU1, connection nipple SA-NIP



Design data PFYN 15 VU1-72 G1/8-IG

Technical data

Attribute	Value
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Size	15.00
Connection	G1/8"-F
Nipple material	Aluminum

Design data

Attribute	Value
Height H	25.50 mm
Nominal diameter dn	2.00 mm
Thread G1	G1/8"-F
Thread length LG1	9.0 mm
Key width SW1	14.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	14.5 mm
Diameter Dmax(S)	17.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.00557

**Technical data**

Attribute	Value
Nipple family	N 005
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	12.5 mm
Suction force (-600mbar)	8.50 N
Weight	7.7 g
Volume	0.500 cm ³
Size	15.00
Number of folds	0.0
Product family	PFYN

Note: Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00557**Ordering Data Spare Parts 10.01.01.00557**

Typ		Item number
Suction cup connection nipple	SA-NIP N005 G1/8-IG DN200	10.01.01.03521
Flat suction cup (round)	PFG 15 VU1-72 N005	10.01.01.00555

**Ordering Data Wear Parts 10.01.01.00557**

Typ		Item number
Flat suction cup (round)	PFG 15 VU1-72 N005	10.01.01.00555

