




PFG 60 VU1-72 N011

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyut	60.00



Tasarım verileri PFG 60 VU1-72 N011

Tasarım verileri

Attribute	Value
Yükseklik H2	8.00 mm
Yükseklik H	18.50 mm
Kafa çapı Dk	20.0 mm
İç çap d1	20.0 mm
İç çap d	8.00 mm
Yay stroku Z	6.5 mm
Çap Ds	60.0 mm
Yükseklik H3	11.00 mm
Çap Dmax(S)	67.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.01.00606

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Emme kuvveti (-600mbar)	130.00 N
Ağırlık	12.5 g
Cilt	15.154 cm ³
Boyut	60.00
Körük Sayısı	0.0
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00606

**Veri aksesuarları sipariş edin 10.01.01.00606**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N011 G1/4-AG DN350
Vantuz bağlantı nipel	SA-NIP N011 G1/4-IG DN350

WWW.SCHMALZ.COM/10.01.01.00606