

Düz vantuz (yuvarlak)

PFG 15 SI-CO-55 N005




Art.-Nr.: 10.01.01.00627



PFG 15 SI-CO-55 N005

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	15,00



Tasarım verileri PFG 15 SI-CO-55 N005

Tasarım verileri

Attribute	Value
Yükseklik H2	2,60 mm
Yükseklik H	8,00 mm
Kafa çapı Dk	12,2 mm
İç çap d1	7,8 mm
İç çap d	4,50 mm
Yay stroku Z	1,9 mm
Çap Ds	15,0 mm
Çap Dmax(S)	17,5 mm
Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları	



WWW.SCHMALZ.COM/10.01.01.00627

Art.-Nr.: 10.01.01.00627

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 005
Vantuz malzemesi	Silikon SI iletken
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Emme kuvveti (-600mbar)	9,00 N
Ağırlık	0,70 g
Cilt	0,432 cm ³
Boyut	15,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00627

**Sipariş Verisi Aksesuarlar 10.01.01.00627**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N005 G1/8-AG DN200
Vantuz bağlantı nipel	SA-NIP N005 G1/8-IG DN200

WWW.SCHMALZ.COM/10.01.01.00627