


Flat suction cup (round)

SGP 35 NK-40 N034


Art.-Nr.: 10.01.01.00788



SGP 35 NK-40 N034

Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	40.0 Shore A
Size	35.00



Design data SGP 35 NK-40 N034

Design data

Attribute	Value
Height H2	14.80 mm
Height H	23.50 mm
Head diameter Dk	16.5 mm
Internal diameter d	10.00 mm
Spring stroke Z	0.5 mm
Diameter Ds	30.2 mm
Diameter Dmax(S)	35.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.00788

Art.-Nr.: 10.01.01.00788

**Technical data**

Attribute	Value
Nipple family	N 034
Suction cup material	Natural rubber NK
Material hardness [Shore A]	40.0 Shore A
Suction force (-600mbar)	31.00 N
Weight	6.4 g
Volume	2.800 cm ³
Size	35.00
Number of folds	0.0
Product family	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00788

**Ordering Data Accessories 10.01.01.00788**

Typ		Item number
Suction cup connection nipple	SA-NIP N034 G1/4-AG DN550	10.01.01.00820
Suction cup connection nipple	SA-NIP N034 G1/4-IG DN550	10.01.01.00819

