

Düz vantuz (yuvarlak)

SGP 30 SI-50 N033




Art.-Nr.: 10.01.01.01064



SGP 30 SI-50 N033

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50,0 Shore A
Boyut	30,00



Tasarım verileri SGP 30 SI-50 N033

Tasarım verileri

Attribute	Value
Yükseklik H2	15,70 mm
Yükseklik H	22,20 mm
Kafa çapı Dk	15,6 mm
İç çap d	11,20 mm
Yay stroku Z	2,0 mm
Çap Ds	30,0 mm
Çap Dmax(S)	32,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.01064

Düz vantuz (yuvarlak)

SGP 30 SI-50 N033



Art.-Nr.: 10.01.01.01064



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 033
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50,0 Shore A
Emme kuvveti (-600mbar)	19,00 N
Ağırlık	3,10 g
Cilt	3,000 cm ³
Boyut	30,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.01064



Sipariş Verisi Aksesuarlar 10.01.01.01064

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N033 G1/4-AG DN550
Vantuz bağlantı nipel	SA-NIP N033 G1/4-IG DN550



WWW.SCHMALZ.COM/10.01.01.01064