



Art.-Nr.: 10.01.01.01089



DR-SPU 210 NBR-55

### Technical data

| Attribute                   | Value              |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 55.0 Shore A       |
| Size                        | 210.00             |



### Design data

| Attribute        | Value    |
|------------------|----------|
| Height H         | 25.50 mm |
| d2               | 163.0 mm |
| Spring stroke Z  | 8.0 mm   |
| Diameter Ds      | 210.0 mm |
| Diameter Dmax(S) | 220.0 mm |

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3

Design data DR-SPU 210 NBR-55



### Technical data

| Attribute                   | Value              |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 55.0 Shore A       |
| Weight                      | 247.10 g           |
| Size                        | 210.00             |
| Product family              | DR-SPU             |

Sealing ring for SPU suction plate

## DR-SPU 210 NBR-55



Art.-Nr.: 10.01.01.01089



**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.01.01089](http://www.schmalz.com/10.01.01.01089)



[WWW.SCHMALZ.COM/10.01.01.01089](http://WWW.SCHMALZ.COM/10.01.01.01089)