




SPC 160 NBR-55 G1/2-IG

Suction plate SPC (sealing ring + support plate) is delivered assembled. The assembly consists of:

- Outer and inner sealing ring of type DR-SPC – elastomer part, available in various diameters
- Aluminium support plate – available with various threads
- Optional product range supplement – touch valve

Available spare parts: sealing ring DR-SPC, touch valve



Design data SPC 160 NBR-55 G1/2-IG

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	160.00
Connection	G1/2-IG

Design data

Attribute	Value
Length L2	36.50 mm
Height H1	26.00 mm
Height H	24.50 mm
d2	113.0 mm
Internal diameter d	34.00 mm
Thread G1	G1/2"-F
Thread length LG1	13.5 mm
Thread G2	G1/4"-F
Thread length LG2	15.0 mm
Hole size d3	88.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.01185

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Suction force (-600mbar)	975.00 N
Weight	450.0 g
Volume	156.134 cm ³
Size	160.00
Number of folds	0.0
Product family	SPC

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.01185

**Ordering Data Accessories 10.01.01.01185**

Typ	Item number
Protection Covers	PC 150 10.01.01.13087

**Ordering Data Spare Parts 10.01.01.01185**

Typ	Item number
Sealing ring for SPC suction plate	DR-SPC 33 HNBR-65 10.01.01.11371

**Ordering Data Wear Parts 10.01.01.01185**

Typ	Item number
Sealing ring for SPC suction plate	DR-SPC 160 NBR-55 10.01.01.01190

