



Art.-Nr.: 10.01.01.03523



SA-NIP N007 G1/8-IG DN350

Technical data

Attribute	Value
Nipple family	N 007
Material	Aluminum
Length L1	24.50 mm
Length L	16.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G1/8"-F
Spanner size SW2	4.0 mm
Fitting length	16.00 mm



Design data SA-NIP N007 G1/8-IG DN350

Design data

Attribute	Value
Length L1	24.50 mm
Length L2	7.00 mm
Length L	16.00 mm
Outside diameter D2	6.5 mm
Outside diameter D	10.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G1/8"-F
Thread length LG1	9.0 mm
Key width SW1	14.0 mm
Spanner size SW2	4.0 mm

**Technical data**

Attribute	Value
Nipple family	N 007
Weight	5.8 g
Material	Aluminum



Art.-Nr.: 10.01.01.03523

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.03523**Ordering Data Accessories 10.01.01.03523**

Typ		Item number
Flat suction cup (round)	PFG 25 FPM-65 N007	10.01.01.00073
Flat suction cup (round)	PFG 25 HT1-60 N007	10.01.01.11164
Flat suction cup (round)	PFG 25 NBR-CO-55 N007	10.01.01.10338
Flat suction cup (round)	PFG 25 NBR-55 N007	10.01.01.00013
Flat suction cup (round)	PFG 25 PU-55 N007	10.01.01.00053
Flat suction cup (round)	PFG 25 SI-55 N007	10.01.01.00033
Flat suction cup (round)	PFG 30 FPM-65 N007	10.01.01.00074
Flat suction cup (round)	PFG 30 HT1-60 N007	10.01.01.11165
Flat suction cup (round)	PFG 30 NBR-CO-55 N007	10.01.01.10339
Flat suction cup (round)	PFG 30 NBR-55 N007	10.01.01.00014
Flat suction cup (round)	PFG 30 PU-55 N007	10.01.01.00054
Flat suction cup (round)	PFG 30 SI-55 N007	10.01.01.00034
Flat suction cup (round)	PFG 35 FPM-65 N007	10.01.01.00075
Flat suction cup (round)	PFG 35 HT1-60 N007	10.01.01.11166
Flat suction cup (round)	PFG 35 NBR-CO-55 N007	10.01.01.10340
Flat suction cup (round)	PFG 35 NBR-55 N007	10.01.01.00015
Flat suction cup (round)	PFG 35 PU-55 N007	10.01.01.00055
Flat suction cup (round)	PFG 35 SI-55 N007	10.01.01.00035
Flat suction cup (round)	PFG 40 FPM-65 N007	10.01.01.00076
Flat suction cup (round)	PFG 40 HT1-60 N007	10.01.01.11167
Flat suction cup (round)	PFG 40 NBR-CO-55 N007	10.01.01.10341
Flat suction cup (round)	PFG 40 NBR-55 N007	10.01.01.00016
Flat suction cup (round)	PFG 40 PU-55 N007	10.01.01.00056
Flat suction cup (round)	PFG 40 SI-55 N007	10.01.01.00036

