


Art.-Nr.: 10.01.01.03526



SA-NIP N004 M5-AG DN200

**Technical data**

| Attribute      | Value    |
|----------------|----------|
| Material       | Aluminum |
| Length L1      | 13.50 mm |
| Thread G1      | M5-M     |
| Fitting length | 5.00 mm  |



Design data SA-NIP N004 M5-AG DN200

**Design data**

| Attribute           | Value    |
|---------------------|----------|
| Length L1           | 13.50 mm |
| Length L2           | 2.00 mm  |
| Length L            | 5.00 mm  |
| Outside diameter D2 | 4.0 mm   |
| Outside diameter D  | 6.00 mm  |
| Nominal diameter dn | 2.00 mm  |
| Thread G1           | M5-M     |
| Thread length LG1   | 4.5 mm   |
| Key width SW1       | 8.0 mm   |
| Length L3           | 2.00 mm  |

**Technical data**

| Attribute     | Value    |
|---------------|----------|
| Nipple family | N 004    |
| Weight        | 1.1 g    |
| Material      | Aluminum |



Art.-Nr.: 10.01.01.03526

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.01.03526](http://www.schmalz.com/10.01.01.03526)**Ordering Data Accessories 10.01.01.03526**

| Typ                      |                       | Item number    |
|--------------------------|-----------------------|----------------|
| Flat suction cup (round) | PFG 10 FPM-65 N004    | 10.01.01.00070 |
| Flat suction cup (round) | PFG 10 HT1-60 N004    | 10.01.01.11161 |
| Flat suction cup (round) | PFG 10 NBR-CO-55 N004 | 10.01.01.10066 |
| Flat suction cup (round) | PFG 10 NBR-55 N004    | 10.01.01.00010 |
| Flat suction cup (round) | PFG 10 PU-55 N004     | 10.01.01.00050 |
| Flat suction cup (round) | PFG 10 SI-CO-55 N004  | 10.01.01.00701 |
| Flat suction cup (round) | PFG 10 SI-55 N004     | 10.01.01.00030 |
| Flat suction cup (round) | PFG 5 FPM-65 N004     | 10.01.01.00067 |
| Flat suction cup (round) | PFG 5 HT1-60 N004     | 10.01.01.11158 |
| Flat suction cup (round) | PFG 5 NBR-CO-55 N004  | 10.01.01.10064 |
| Flat suction cup (round) | PFG 5 NBR-55 N004     | 10.01.01.00007 |
| Flat suction cup (round) | PFG 5 SI-CO-55 N004   | 10.01.01.10051 |
| Flat suction cup (round) | PFG 5 SI-55 N004      | 10.01.01.00027 |
| Flat suction cup (round) | PFG 6 FPM-65 N004     | 10.01.01.00068 |
| Flat suction cup (round) | PFG 6 HT1-60 N004     | 10.01.01.11159 |
| Flat suction cup (round) | PFG 6 NBR-CO-55 N004  | 10.01.01.10065 |
| Flat suction cup (round) | PFG 6 NBR-55 N004     | 10.01.01.00008 |
| Flat suction cup (round) | PFG 6 SI-CO-55 N004   | 10.01.01.00626 |
| Flat suction cup (round) | PFG 6 SI-55 N004      | 10.01.01.00028 |
| Flat suction cup (round) | PFG 8 FPM-65 N004     | 10.01.01.00069 |
| Flat suction cup (round) | PFG 8 HT1-60 N004     | 10.01.01.11160 |
| Flat suction cup (round) | PFG 8 NBR-CO-55 N004  | 10.01.01.10043 |
| Flat suction cup (round) | PFG 8 NBR-55 N004     | 10.01.01.00009 |
| Flat suction cup (round) | PFG 8 PU-55 N004      | 10.01.01.00049 |
| Flat suction cup (round) | PFG 8 SI-CO-55 N004   | 10.01.01.00647 |
| Flat suction cup (round) | PFG 8 SI-55 N004      | 10.01.01.00029 |

