

Düz vantuz (yuvarlak)

PFG 2 SI-CO-55 N003


Art.-Nr.: 10.01.01.10050



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	2,00

PFG 2 SI-CO-55 N003



Tasarım verileri

Attribute	Value
Yükseklik H2	1,50 mm
Yükseklik H	4,00 mm
Kafa çapı Dk	4,2 mm
İç çap d1	3,0 mm
İç çap d	2,00 mm
Yay stroku Z	0,5 mm
Çap Ds	2,0 mm
Yükseklik H3	2,50 mm
Çap Dmax(S)	3,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri PFG 2 SI-CO-55 N003



WWW.SCHMALZ.COM/10.01.01.10050

Art.-Nr.: 10.01.01.10050

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 003
Vantuz malzemesi	Silikon SI iletken
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	2,0 mm
Emme kuvveti (-600mbar)	0,12 N
Ağırlık	0,10 g
Cilt	0,014 cm ³
Boyut	2,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10050

**Sipariş Verisi Aksesuarlar 10.01.01.10050**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N003 M3-AG DN100
	10.01.01.00316

WWW.SCHMALZ.COM/10.01.01.10050