

Düz vantuz (yuvarlak)

SGP 24 NK-40 N016




Art.-Nr.: 10.01.01.10320



SGP 24 NK-40 N016

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	40,0 Shore A
Boyut	24,00



Tasarım verileri SGP 24 NK-40 N016

Tasarım verileri

Attribute	Value
Yükseklik H2	7,30 mm
Yükseklik H	10,80 mm
Kafa çapı Dk	10,5 mm
İç çap d	4,50 mm
Yay stroku Z	1,7 mm
Çap Ds	24,0 mm
Çap Dmax(S)	25,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.10320

Düz vantuz (yuvarlak)

SGP 24 NK-40 N016



Art.-Nr.: 10.01.01.10320



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	40,0 Shore A
Emme kuvveti (-600mbar)	11,00 N
Ağırlık	1,10 g
Cilt	0,851 cm ³
Boyut	24,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10320



Sipariş Verisi Aksesuarlar 10.01.01.10320

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N016 M5-AG DN250



WWW.SCHMALZ.COM/10.01.01.10320