

Düz vantuz (yuvarlak)

PFG 25 NBR-CO-55 N007




Art.-Nr.: 10.01.01.10338



PFG 25 NBR-CO-55 N007

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	25,00



Tasarım verileri PFG 25 NBR-CO-55 N007

Tasarım verileri

Attribute	Value
Yükseklik H2	7,00 mm
Yükseklik H	14,00 mm
Kafa çapı Dk	16,2 mm
İç çap d1	11,0 mm
İç çap d	6,00 mm
Yay stroku Z	3,0 mm
Çap Ds	25,0 mm
Çap Dmax(S)	27,5 mm
Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları	



WWW.SCHMALZ.COM/10.01.01.10338

Art.-Nr.: 10.01.01.10338

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 007
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	25,0 mm
Emme kuvveti (-600mbar)	26,50 N
Ağırlık	2,40 g
Cilt	1,483 cm ³
Boyut	25,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10338

**Sipariş Verisi Aksesuarlar 10.01.01.10338**

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N007 G1/8-AG DN240	10.01.01.03531
Vantuz bağlantı nipeli	SA-NIP N007 G1/8-IG DN350	10.01.01.03523
Vantuz kapağı	SU 25	10.01.01.13584

