


Düz vantuz (yuvarlak)

PFG 40 NBR-CO-55 N007


Art.-Nr.: 10.01.01.10341



PFG 40 NBR-CO-55 N007

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	40,00



Tasarım verileri PFG 40 NBR-CO-55 N007

Tasarım verileri

Attribute	Value
Yükseklik H2	7,00 mm
Yükseklik H	14,00 mm
Kafa çapı Dk	24,3 mm
İç çap d1	11,0 mm
İç çap d	6,00 mm
Yay stroku Z	3,5 mm
Çap Ds	40,0 mm
Çap Dmax(S)	43,0 mm
Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları	



WWW.SCHMALZ.COM/10.01.01.10341

Art.-Nr.: 10.01.01.10341

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 007
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	57,70 N
Ağırlık	7,50 g
Cilt	3,912 cm ³
Boyut	40,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10341

**Sipariş Verisi Aksesuarlar 10.01.01.10341**

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N007 G1/8-AG DN240	10.01.01.03531
Vantuz bağlantı nipeli	SA-NIP N007 G1/8-IG DN350	10.01.01.03523
Vantuz kapağı	SU 40	10.01.01.12856

