

Düz vantuz (yuvarlak)

PFG 50 NBR-CO-55 N008


Art.-Nr.: 10.01.01.10342



PFG 50 NBR-CO-55 N008

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	50,00



Tasarım verileri PFG 50 NBR-CO-55 N008

Tasarım verileri

Attribute	Value
Yükseklik H2	7,00 mm
Yükseklik H	15,00 mm
Kafa çapı Dk	29,1 mm
İç çap d1	20,0 mm
İç çap d	8,00 mm
Yay stroku Z	4,0 mm
Çap Ds	50,0 mm
Çap Dmax(S)	53,5 mm
Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları	



WWW.SCHMALZ.COM/10.01.01.10342

Art.-Nr.: 10.01.01.10342

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 008
Vantuz malzemesi	Nitril kauçuk NBR-iletken
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	91,00 N
Ağırlık	10,20 g
Cilt	7,076 cm ³
Boyut	50,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10342

**Sipariş Verisi Aksesuarlar 10.01.01.10342**

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N008 G1/8-AG DN350	10.01.01.03532
Vantuz bağlantı nipeli	SA-NIP N008 G1/8-IG DN350	10.01.01.03524
Vantuz kapağı	SU 50	10.01.01.12837

