

Art.-Nr.: 10.01.01.10527




DI-PROF 9x9.7 2K-MOS CR-20/60

Sealing profile DI-PROF is delivered in the desired length. Accounting unit 1 m.

Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Sealing material	Chloroprene CR
Width B	9.00 mm
Height H	9.70 mm



Design data DI-PROF 9x9.7 2K-MOS CR-20/60

Design data

Attribute	Value
Width B1	14.50 mm
Width B2	3.90 mm
Width B	9.00 mm
Height H1	26.50 mm
Height H2	2.00 mm
Height H	9.70 mm
Width B3	5.90 mm
Width B4	9.60 mm
Height H3	4.70 mm
Height H4	10.00 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Sealing profile (meter)

DI-PROF 9x9.7 2K-MOS CR-20/60



Art.-Nr.: 10.01.01.10527



Technical data

Attribute	Value
Material hardness [Shore A]	20.0 Shore A
Weight	310.0 g
Sealing material	Chloroprene CR
Product family	DI-PROF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10527



WWW.SCHMALZ.COM/10.01.01.10527