

Flat suction cup (round)

SGP 24 SI-50 N016


Art.-Nr.: 10.01.01.10577



SGP 24 SI-50 N016

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	50.0 Shore A
Size	24.00



Design data

Attribute	Value
Height H2	7.30 mm
Height H	10.80 mm
Head diameter Dk	10.5 mm
Internal diameter d	4.50 mm
Spring stroke Z	1.7 mm
Diameter Ds	24.0 mm
Diameter Dmax(S)	25.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGP 24 SI-50 N016



WWW.SCHMALZ.COM/10.01.01.10577

Flat suction cup (round)

SGP 24 SI-50 N016



Art.-Nr.: 10.01.01.10577



Technical data

Attribute	Value
Nipple family	N 016
Suction cup material	Silicone SI
Material hardness [Shore A]	50.0 Shore A
Suction force (-600mbar)	11.00 N
Weight	1.1 g
Volume	0.851 cm ³
Size	24.00
Number of folds	0.0
Product family	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10577



Ordering Data Accessories 10.01.01.10577

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123



WWW.SCHMALZ.COM/10.01.01.10577