


Düz vantuz (yuvarlak)

SGP 34 NK-40 N033


Art.-Nr.: 10.01.01.10829



SGP 34 NK-40 N033

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	40,0 Shore A
Boyut	34,00



Tasarım verileri SGP 34 NK-40 N033

Tasarım verileri

Attribute	Value
Yükseklik H2	16,80 mm
Yükseklik H	23,00 mm
Kafa çapı Dk	15,2 mm
İç çap d	11,20 mm
Yay stroku Z	2,2 mm
Çap Ds	34,0 mm
Çap Dmax(S)	37,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.10829

Düz vantuz (yuvarlak)

SGP 34 NK-40 N033



Art.-Nr.: 10.01.01.10829



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 033
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	40,0 Shore A
Emme kuvveti (-600mbar)	25,00 N
Ağırlık	5,60 g
Cilt	3,700 cm ³
Boyut	34,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10829



Sipariş Verisi Aksesuarlar 10.01.01.10829

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N033 G1/4-AG DN550
Vantuz bağlantı nipel	SA-NIP N033 G1/4-IG DN550



WWW.SCHMALZ.COM/10.01.01.10829