

Flat suction cup (round)

SHF 70 NK-45 N041


Art.-Nr.: 10.01.01.11682



SHF 70 NK-45 N041

Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	70.00



Design data SHF 70 NK-45 N041

Design data

Attribute	Value
Height H2	12.80 mm
Height H	22.20 mm
Head diameter Dk	17.0 mm
Internal diameter d1	17.0 mm
d2	48.0 mm
Internal diameter d	7.50 mm
Spring stroke Z	4.0 mm
Diameter Ds	70.0 mm
Height H3	14.30 mm
Diameter Dmax(S)	74.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.11682

Art.-Nr.: 10.01.01.11682

**Technical data**

Attribute	Value
Nipple family	N 041
Suction cup material	Natural rubber NK
Workpiece radius min. (convex)	95.0 mm
Suction force (-600mbar)	155.00 N
Weight	28.2 g
Lateral force	145.0 N
Volume	16.207 cm ³
Size	70.00
Number of folds	0.0
Product family	SHF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.11682

**Ordering Data Accessories 10.01.01.11682**

Typ		Item number
Suction cup connection nipple	SA-NIP N041 G1/4-AG DN440	10.01.01.11772
Suction cup connection nipple	SA-NIP N041 G1/4-IG DN440	10.01.01.11822
Sieve, round	SIEB 15x0.8 MS-A2 0.103/0.07	10.07.01.00211
Touch Valve	TVN G1/4-AG 8.4 N041	10.05.10.00058

