

Flat suction cup (round)

SHF 50 NK-45 N041 MOS


Art.-Nr.: 10.01.01.11688



SHF 50 NK-45 N041 MOS

Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	50.00



Design data SHF 50 NK-45 N041 MOS

Design data

Attribute	Value
Height H2	12.80 mm
Height H	22.20 mm
Head diameter Dk	17.0 mm
Internal diameter d1	17.0 mm
d2	21.0 mm
Internal diameter d	7.50 mm
Spring stroke Z	3.0 mm
Diameter Ds	52.0 mm
Height H3	14.30 mm
Diameter Dmax(S)	55.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.11688

Art.-Nr.: 10.01.01.11688

**Technical data**

Attribute	Value
Nipple family	N 041
Suction cup material	Natural rubber NK
Workpiece radius min. (convex)	41.0 mm
Suction force (-600mbar)	90.00 N
Weight	15.70 g
Lateral force	95.0 N
Volume	7.240 cm ³
Size	50.00
Number of folds	0.0
Product family	SHF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.11688

**Ordering Data Accessories 10.01.01.11688**

Typ		Item number
Suction cup connection nipple	SA-NIP N041 G1/4-AG DN440	10.01.01.11772
Suction cup connection nipple	SA-NIP N041 G1/4-IG DN440	10.01.01.11822
Sieve, round	SIEB 15x0.8 MS-A2 0.103/0.07	10.07.01.00211
Touch Valve	TVN G1/4-AG 8.4 N041	10.05.10.00058

**Ordering Data Wear Parts 10.01.01.11688**

Typ		Item number
Sealing ring	DR 28/21x3 C03 EPDM-15 KE	10.01.06.01679

