

Düz vantuz (yuvarlak)

SAFT 80 NBR-60


Art.-Nr.: 10.01.01.11939



SAFT 80 NBR-60

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	80,00



Tasarım verileri SAFT 80 NBR-60

Tasarım verileri

Attribute	Value
Yükseklik H	36,00 mm
Kafa çapı Dk	40,0 mm
İç çap d	19,00 mm
Yay stroku Z	7,3 mm
Çap Ds	83,0 mm
Çap Dmax(S)	86,0 mm



WWW.SCHMALZ.COM/10.01.01.11939

Düz vantuz (yuvarlak)

SAFT 80 NBR-60



Art.-Nr.: 10.01.01.11939



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Ağırlık	53,20 g
Boyut	80,00
Körük Sayısı	0,0
Ürün ailesi	SAFT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.11939



WWW.SCHMALZ.COM/10.01.01.11939