

Çan vantuz (yuvarlak)

SAG 45 NBR-60 RA




Art.-Nr.: 10.01.01.12162



SAG 45 NBR-60 RA

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	45,00
Bağlantı	RA
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAG 45 NBR-60 RA

Tasarım verileri

Attribute	Value
Yükseklik H	27,70 mm
Nominal çap dn	4,00 mm
Yay stroku Z	7,8 mm
Çap Ds	47,0 mm
Uzunluk L4	31,80 mm
Çap Dmax(S)	51,5 mm



WWW.SCHMALZ.COM/10.01.01.12162

Art.-Nr.: 10.01.01.12162

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	40,0 mm
Emme kuvveti (-600mbar)	68,00 N
Ağırlık	27,20 g
Yanal kuvvet	61,0 N
Yanal kuvvet yağlı yüzey	51,0 N
Cilt	8,000 cm ³
Boyut	45,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12162

**Sipariş Verisi Yedek Parça 10.01.01.12162**

Typ	Ürün numarası
Montaj adaptörü	ADP-A G1/4-AG-RA ADAP 10.01.10.00235
O-ring	O-RING 19x3.2 NBR-70 10.07.08.00123

