


Flat suction cup (round)

SHF 70 NK-45 M10x1.25-IG E

Art.-Nr.: 10.01.01.12165



SHF 70 NK-45 M10x1.25-IG E



Design data SHF 70 NK-45 M10x1.25-IG E

Technical data

Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	70.00
Thread G1	M10x1.25-F
Type	E

Design data

Attribute	Value
Height H	18.10 mm
d2	48.0 mm
Thread G1	M10x1.25-F
Thread length LG1	10.0 mm
Spring stroke Z	4.0 mm
Diameter Ds	70.0 mm
Diameter Dmax(S)	74.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.12165

Art.-Nr.: 10.01.01.12165

**Technical data**

Attribute	Value
Suction cup material	Natural rubber NK
Suction force (-600mbar)	155.00 N
Weight	52.5 g
Volume	16.100 cm ³
Size	70.00
Number of folds	0.0
Product family	SHF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12165

**Ordering Data Accessories 10.01.01.12165**

Typ		Item number
Reduction nipple with hexagon	RED-NIP G1/4-AG M10x1.25-AG AL	10.01.01.12194
Suction cup connection nipple	SA-NIP N009 G1/4-IG DN440	10.01.01.12192
Sieve, round	SIEB 14.5x1 MS-A2 0.103/0.15	10.05.03.00023
Touch Valve	TVN G1/4-AG 9 N009	10.05.10.00065