




SAG 60 NBR-60 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	60,00
Bağlantı	G3/8-IG
Meme ucu malzemesi	Alüminyum



Tasarım verileri

Attribute	Value
Yükseklik H	31,00 mm
Nominal çap dn	6,00 mm
Diş G1	G3/8"-F
Diş uzunluğu LG1	15,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	10,6 mm
Çap Ds	63,5 mm
Çap Dmax(S)	70,5 mm

Tasarım verileri SAG 60 NBR-60 G3/8-IG

Art.-Nr.: 10.01.01.12166

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	122,00 N
Ağırlık	31,10 g
Yanal kuvvet	153,0 N
Yanal kuvvet yağlı yüzey	80,0 N
Cilt	22,000 cm ³
Boyut	60,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12166

WWW.SCHMALZ.COM/10.01.01.12166