




SAG 60 NBR-60 RA

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	60,00
Bağlantı	RA
Meme ucu malzemesi	Alüminyum



Tasarım verileri

Attribute	Value
Yükseklik H	30,70 mm
Nominal çap dn	6,00 mm
Yay stroku Z	10,6 mm
Çap Ds	63,5 mm
Uzunluk L4	31,80 mm
Çap Dmax(S)	70,5 mm

Tasarım verileri SAG 60 NBR-60 RA

Art.-Nr.: 10.01.01.12169

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	122,00 N
Ağırlık	40,10 g
Yanal kuvvet	153,0 N
Yanal kuvvet yağlı yüzey	80,0 N
Cilt	22,000 cm ³
Boyut	60,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12169

**Sipariş Verisi Yedek Parça 10.01.01.12169**

Typ	Ürün numarası
Montaj adaptörü	ADP-A G3/8-AG-RA ADAP 10.01.10.00234
O-ring	O-RING 19x3.2 NBR-70 10.07.08.00123

