




SAG 80 NBR-60 G1/4-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	80,00
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum



Tasarım verileri

Attribute	Value
Yükseklik H	35,00 mm
Nominal çap dn	6,00 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	12,8 mm
Çap Ds	83,0 mm
Çap Dmax(S)	90,7 mm

Tasarım verileri SAG 80 NBR-60 G1/4-AG

Art.-Nr.: 10.01.01.12171

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	70,0 mm
Emme kuvveti (-600mbar)	217,00 N
Ağırlık	23,40 g
Yanal kuvvet	284,0 N
Yanal kuvvet yağlı yüzey	167,0 N
Cilt	44,000 cm ³
Boyut	80,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12171

WWW.SCHMALZ.COM/10.01.01.12171