


Çan vantuz (oval)

SAOG-S 60x20 NBR-60 RA




Art.-Nr.: 10.01.01.12176



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Bağlantı	RA
Boyutlar (LxW)	60x20
Meme ucu malzemesi	Alüminyum

SAOG-S 60x20 NBR-60 RA



Tasarım verileri

Attribute	Value
Yükseklik H	23,50 mm
Nominal çap dn	4,00 mm
Yay stroku Z	5,0 mm
Uzunluk L4	31,80 mm
Vantuz genişliği Bs	20,90 mm
Ls	60,90 mm
Lmaks.(S)	65,80 mm
Bmax(S)	25,80 mm

Tasarım verileri SAOG-S 60x20 NBR-60 RA



WWW.SCHMALZ.COM/10.01.01.12176

Art.-Nr.: 10.01.01.12176

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Emme kuvveti (-600mbar)	56,00 N
Ağırlık	27,60 g
Boyutlar (LxW)	60 x 20
Yanal kuvvet	45,0 N
Yanal kuvvet yağlı yüzey	30,0 N
Cilt	4,000 cm ³
Körük Sayısı	0,0
Ürün ailesi	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12176

**Sipariş Verisi Yedek Parça 10.01.01.12176**

Typ	Ürün numarası
Montaj adaptörü	ADP-A G1/8-AG-RA ADAP
O-ring	O-RING 10x1.5 NBR-70 GLB
O-ring	O-RING 19x3.2 NBR-70

