


Bell suction cup (oval)

SAOG-S 60x20 NBR-60 RA


Art.-Nr.: 10.01.01.12176



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Connection	RA
Dimension (LxW)	60x20
Nipple material	Aluminum

SAOG-S 60x20 NBR-60 RA



Design data

Attribute	Value
Height H	23.50 mm
Nominal diameter dn	4.00 mm
Spring stroke Z	5.0 mm
Length L4	31.80 mm
Suction cup width Bs	20.90 mm
Ls	60.90 mm
Lmax.(S)	65.80 mm
Bmax(S)	25.80 mm

Design data SAOG-S 60x20 NBR-60 RA



WWW.SCHMALZ.COM/10.01.01.12176

Art.-Nr.: 10.01.01.12176

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	12.5 mm
Suction force (-600mbar)	56.00 N
Weight	27.6 g
Dimension (LxW)	60 x 20
Lateral force	45.0 N
Lateral force oily surface	30.0 N
Volume	4.000 cm ³
Number of folds	0.0
Product family	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12176

**Ordering Data Spare Parts 10.01.01.12176**

Typ		Item number
Mounting adapter	ADP-A G1/8-AG-RA ADAP	10.01.10.00210
O-ring	O-RING 10x1.5 NBR-70 GLB	10.07.08.00129
O-ring	O-RING 19x3.2 NBR-70	10.07.08.00123

