

Düz vantuz (yuvarlak)

SHF 85 NK-45 M10x1.25-IG E MOS




Art.-Nr.: 10.01.01.12223



SHF 85 NK-45 M10x1.25-IG E MOS

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	85,00
Diş G1	M10x1.25-F
Tip	E



Tasarım verileri SHF 85 NK-45 M10x1.25-IG E MOS

Tasarım verileri

Attribute	Value
Yükseklik H	18,10 mm
d2	50,0 mm
Diş G1	M10x1.25-F
Diş uzunluğu LG1	10,0 mm
Yay stroku Z	4,0 mm
Çap Ds	85,0 mm
Çap Dmax(S)	89,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.12223

SHF 85 NK-45 M10x1.25-IG E MOS

Art.-Nr.: 10.01.01.12223



Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Emme kuvveti (-600mbar)	198,00 N
Ağırlık	97,8 g
Cilt	20,100 cm ³
Boyut	85,00
Körük Sayısı	0,0
Ürün ailesi	SHF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12223



Sipariş Verisi Aksesuarlar 10.01.01.12223

Typ	Ürün numarası
Altıgen redüksiyon nipel	RED-NIP G1/4-AG M10x1.25-AG AL 10.01.01.12194
Vantuz bağlantı nipel	SA-NIP N009 G1/4-IG DN440 10.01.01.12192
Elek, yuvarlak	SIEB 14.5x1 MS-A2 0.103/0.15 10.05.03.00023
Temas Valfi	TVN G1/4-AG 9 N009 10.05.10.00065



Sipariş Verisi Aşınma Parçaları 10.01.01.12223

Typ	Ürün numarası
Sızdırmazlık halkası	DR 60/50x5 S05 EPDM-15 KE 10.01.06.01720

WWW.SCHMALZ.COM/10.01.01.12223