




SAG 60 NBR-60 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	60.00
Bağlantı	G1/4-IG
Meme ucu malzemesi	Alüminyum



Tasarım verileri

Attribute	Value
Yükseklik H	36.00 mm
Nominal çap dn	6.00 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	15.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	10.6 mm
Çap Ds	63.5 mm
Çap Dmax(S)	70.5 mm

Tasarım verileri SAG 60 NBR-60 G1/4-IG

Art.-Nr.: 10.01.01.12267



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Emme kuvveti (-600mbar)	122.00 N
Ağırlık	44.9 g
Yanal kuvvet	153.0 N
Yanal kuvvet yağlı yüzey	80.0 N
Cilt	22.000 cm ³
Boyut	60.00
Körük Sayısı	0.0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12267



WWW.SCHMALZ.COM/10.01.01.12267