




SAG 45 NBR-60 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	45,00
Bağlantı	M10-AG
Meme ucu malzemesi	Çelik



Tasarım verileri SAG 45 NBR-60 M10-AG

Tasarım verileri

Attribute	Value
Yükseklik H	36,50 mm
Nominal çap dn	4,00 mm
Diş G1	M10-M
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	7,8 mm
Çap Ds	47,0 mm
Çap Dmax(S)	51,5 mm

Art.-Nr.: 10.01.01.12296



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Emme kuvveti (-600mbar)	68,00 N
Ağırlık	27,80 g
Boyut	45,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12296



WWW.SCHMALZ.COM/10.01.01.12296