




SAG 60 NBR-60 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	60,00
Bağlantı	M10-AG
Meme ucu malzemesi	Çelik



Tasarım verileri

Attribute	Value
Yükseklik H	43,20 mm
Nominal çap dn	4,00 mm
Diş G1	M10-M
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	10,6 mm
Çap Ds	63,5 mm
Çap Dmax(S)	70,5 mm

Tasarım verileri SAG 60 NBR-60 M10-AG

Art.-Nr.: 10.01.01.12297



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Emme kuvveti (-600mbar)	122,00 N
Ağırlık	54,40 g
Boyut	60,00
Körük Sayısı	0,0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12297



WWW.SCHMALZ.COM/10.01.01.12297