




SAG 80 NBR-60 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	80.00
Bağlantı	M10-AG
Meme ucu malzemesi	Çelik



Tasarım verileri

Attribute	Value
Yükseklik H	35.00 mm
Nominal çap dn	4.00 mm
Diş G1	M10-M
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	12.8 mm
Çap Ds	83.0 mm
Çap Dmax(S)	90.7 mm

Tasarım verileri SAG 80 NBR-60 M10-AG

Art.-Nr.: 10.01.01.12301



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60.0 Shore A
Emme kuvveti (-600mbar)	217.00 N
Ağırlık	68.6 g
Boyut	80.00
Körük Sayısı	0.0
Ürün ailesi	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12301

