


Art.-Nr.: 10.01.01.12302



SAOG-S 60x20 NBR-60 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60.0 Shore A
Bağlantı	M10-AG
Boyutlar (LxW)	60x20
Meme ucu malzemesi	Çelik



Tasarım verileri SAOG-S 60x20 NBR-60 M10-AG

Tasarım verileri

Attribute	Value
Yükseklik H	32.50 mm
Nominal çap dn	5.10 mm
Diş G1	M10-M
Diş uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	16.0 mm
Yay stroku Z	5.0 mm
Vantuz genişliği Bs	20.90 mm
Ls	60.90 mm
Lmaks.(S)	65.80 mm
Bmax(S)	25.80 mm

Art.-Nr.: 10.01.01.12302

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	12.5 mm
Emme kuvveti (-600mbar)	56.00 N
Ağırlık	26.5 g
Boyutlar (LxW)	60 x 20
Yanal kuvvet	45.0 N
Yanal kuvvet yağlı yüzey	30.0 N
Cilt	4.000 cm ³
Körük Sayısı	0.0
Ürün ailesi	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12302

WWW.SCHMALZ.COM/10.01.01.12302